

## Sylmaster LED


SYLMASTER T8 LED 1500 1L 2000lm 4K

0051682



### Product features

- SYLMASTER T8 LED 1500 SO 4K is a surface mount / pendant luminaire supplied with ToLEDo T8 25.5W 840 LED Tube. (0029298)



### PRODUCT OVERVIEW

Product name	SYLMASTER T8 LED 1500 1L 2000lm 4K
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
Warranty	3 years
Fixture luminous flux (lm)	2000
Luminaire efficacy (lm/W)	74
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Glare control	< 21
Photobiological Risk Group	RG0
Light source included	0029298
Total power consumption (W)	27
Electrical protection	Class I
Control gear type	Electronic ballast
Dimmable	No
Dimming method	N/A
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5410288516820

### DATA TABLE

General data

## Sylmaster LED

SYLMASTER T8 LED 1500 1L 2000lm 4K

0051682

Product name	SYLMASTER T8 LED 1500 1L 2000lm 4K
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Education, Hospitality, Office, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	3 years

### Optical data

Fixture luminous flux (lm)	2000
Luminaire efficacy (lm/W)	74
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Glare control	< 21
Photobiological Risk Group	RG0

### Electrical data

Light source included	0029298
Total power consumption (W)	27
Mains voltage (V)	220-240V
Lamp power factor	0.9
Electrical protection	Class I
Control gear required	No
Control gear type	Electronic ballast
No. Of switching cycles before premature failures	>200000
Dimmable	No
Dimming method	N/A
Drive current (mA)	95
Glow Wire Test (°C)	850
Energy Efficiency Class (A->G) of contained light source	F
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	40000
------------------	-------

### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser finish	Transparent
Nominal Product Length (mm)	1550
Nominal Product Width (mm)	202

## Sylmaster LED



SYLMASTER T8 LED 1500 1L 2000lm 4K  
0051682

Nominal Product Height (mm)	85
Weight (kg)	5.364


### Packaging

Single packaging type	Carton
Product EAN number	5410288516820
Packaging single length / height (cm)	155.0
Packaging single width (cm)	9.0
Packaging single depth (cm)	21.0
DUN14 (outer)	05410288516820
Units per outer package	1
Packaging outer length / height (cm)	155.0
Packaging outer width (cm)	9.0
Packaging outer depth (cm)	21.0

## PHOTOMETRY



## TECHNICAL DRAWINGS



Version	L	W	F	H
1x36W	1250	202	1000	85
1x58W	1550	202	1000	85
2x36W	1250	202	1000	85
2x58W	1550	202	1000	85