

## Video infrared temperature measuring device with integrated humidity sensor

**ORION**<sup>®</sup>

### Application:

For non-contact measuring of dew points and surface temperatures. Ideal for indoor climate specialists. Indoor climate measurements

### Execution:

- Double target laser
- HOLD, MAX, MIN functions
- Switch display between °C/F
- USB port
- Error limit  $\pm 2\%$  or  $\pm 2^\circ\text{C}$

### Advantage:

- Large 2.2 inch TFT colour display
- Input for thermocouple sensor NiCrNi (type K)
- Large measured value memory (micro-SD card slot)
- IR temperature measuring device with integrated humidity sensor
- Applications are displayed as JPG images with measured values and date stamps

### Delivery:

Sturdy transport case, USB cable, mains plug with USB connection, incl. temperature sensor TYP K, small camera tripod



<b>Art. no.</b>	<b>46135 100</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	46135100
<b>Min./max. temperature measuring range</b>	-50 to 1000 °C
<b>Optical focus</b>	50:1
<b>Gross Weight</b>	2.108 kg
<b>Product Group</b>	456

### EAN

4053625048342