

## ESD shelf trolley 9000 series, load capacity 300 kg

In 4 sizes and with 2, 3 and 4 load areas



### Application:

Ideal as a transport and picking trolley for many types of goods, including sensitive electrical equipment.

### Execution:

- Electrolytically galvanised, highly stable tubular frame structure with front and rear grid
- Electrically conductive load areas, SP tested and heat-resistant up to 400°C

### Advantage:

- Continuously height-adjustable load areas
- Ergonomic - height-adjustable push handle
- Helps to transport goods more efficiently



<b>Art. no.</b>	<b>50290 051</b>
<b>Brand</b>	KONGAMEK
<b>Manufacturer Part Number</b>	KM9000-4XL-ESD
<b>Load-carrying capacity</b>	300 kg
<b>Load-carrying capacity of loading surfaces</b>	100 kg
<b>Colour</b>	Silver coloured
<b>Material of loading surface</b>	Wood, electroconductive
<b>Number of loading surfaces</b>	4
<b>Loading surface length</b>	1790 mm
<b>ESD-capable</b>	Yes
<b>Loading-surface width</b>	650 mm
<b>Length</b>	1790 mm
<b>Width</b>	650 mm
<b>Height</b>	1590 mm
<b>Loading surface size</b>	1790 x 650 mm
<b>Surface</b>	Zinc plated
<b>Length x width x height</b>	1790 x 650 x 1590 mm
<b>With wheel lock</b>	No
<b>Wheel diameter</b>	160 mm
<b>Material of wheel</b>	Solid rubber
<b>Number of steering rollers</b>	4
<b>Made in</b>	Sweden
<b>Gross Weight</b>	64.000 kg
<b>Product Group</b>	5AT

### EAN

7350074809119