

Art. no.	50639 325
Model	25
Door design	Perforated plates/slotted plates
Height	1950 mm
Width	1130 mm
Depth	590 mm
Number of shelves, depth 250 mm	3
Number of shelves, depth 340 mm	3
Number of shelves, depth 530 mm	1
Number of bins 85 x 105 x 45 mm	32
Number of bins 160 x 105 x 75 mm	50
Number of bins 230 x 140 x 130 mm	14
Number of bins 290 x 140 x 130 mm	7
Number of bins 350 x 200 x 150 mm	15
Number of drawers	4
Drawer front height	4 x 125 mm
Pullout type	Full extension
Load-carrying capacity per shelf	50 kg
Load-carrying capacity per drawer	50 kg
Lock type	Cylinder lock
Material	Sheet steel
Body colour	Light grey RAL 7035
Colour of front	Light grey RAL 7035
Surface	Plastic-coated



EAN-Code

4251142219799