

Sheet metal punches, Tristar

12.5 to 63 mm



Application:

For punching holes in sheet metal.

Version:

- Sheet hole-punch system with slug splitter for standard steel S235
- Burr-free hole punching
- Actuated using a wrench, hydraulic punch or cordless compact punch
- When actuated with a wrench, draw bolts with ball bearings must be used

Advantage:

- The sheet does not jam in the centre thanks to the triple partition

Delivery:

Stamp and die – screw or tension bolt has to be ordered separately



Art. no.	53829 125
Diameter	12.5 mm
Suitable for max. sheet metal thickness	1.5 mm
Screw diameter	6 mm
Screw length	40 mm

EAN-Code

4030266122648