

Sheet metal punches, Tristar

12.5 to 63 mm



Application:

For punching holes in sheet metal.

Execution:

- Sheet hole-punch system with slug splitter for standard steel S235
- Burr-free hole punching
- Actuated using a wrench, hydraulic punch or cordless compact punch
- When actuated with a wrench, draw bolts with ball bearings must be used

Advantage:

- The sheet does not jam in the centre thanks to the triple partition

Delivery:

Stamp and die – screw or tension bolt has to be ordered separately



Art. no.	53829 125
Brand	ALFRA
Manufacturer Part Number	01770
Diameter	12.5 mm
Suitable for max. sheet metal thickness	1.5 mm
Screw diameter	6 mm
Screw length	40 mm
Gross Weight	0.039 kg
Product Group	554

EAN

4030266 122648

