

## Pneumatic torque screwdriver RRI-SP20705

Pistol version - with shut-off



### Application:

Developed for the assembly industry

### Execution:

- Pistol version
- Ergonomic handle
- Left and right rotation
- Noise-dampened and rotating rear air outlet
- Housing made of composite

### Advantage:

- High torque, very accurate and low vibration
- Easy to adjust
- Shut-off coupling combines low reaction forces with high repeat accuracy



<b>Art. no.</b>	<b>75066 380</b>
<b>Brand</b>	RED ROOSTER
<b>Manufacturer Part Number</b>	RRI-SP20705
<b>Model</b>	RRI-SP20705
<b>Type</b>	Pistol version
<b>Suitable for screw</b>	M4
<b>Min. tightening torque</b>	1.5 Nm
<b>Max. tightening torque</b>	4.5 Nm
<b>Min./max. tightening torque</b>	1.5-4.5 Nm
<b>Max. idle speed</b>	700 rpm
<b>Max. torque</b>	4.5 Nm
<b>Air consumption</b>	10 l/s
<b>Tool holding device</b>	1/4-inch hexagon socket
<b>Connection thread</b>	1/4 inch
<b>Inner hose diameter</b>	6.5 mm
<b>Sound-pressure level</b>	72 dB
<b>Length</b>	209 mm
<b>Weight</b>	0.98 kg
<b>Coupling design</b>	Cut-off clutch
<b>Gross Weight</b>	0.980 kg
<b>Product Group</b>	7AE

### EAN

8717981279210