

## VIP sling chains, quality class 10, 4-stranded

Cannot be shortened



### Application:

For the safe and regulatory-compliant lifting of heavy loads.

### Execution:

- CrNiMo stainless steel, special hardening and tempering, quality class 10
- Bright fluorescent pink powder coating (VIP)
- VIP-identification label with integrated chain test gauge, to check the three deposit criteria for sling chains (diameter wear, pitch extension and overload)
- VIP-Cobra safety hook with patented wear marks showing the legal deposit maturity without measuring, marking points for check dimension of the jaw width
- Integrated heat indicator: in the event of inadmissible overheating above 400°C, the colour changes to jet black and small bubbles form
- 4 chain strands with fixed length

### Advantage:

- Up to 30% higher carrying capacity compared to quality class 8 with the same nominal chain thickness
- No confusion with other quality classes
- Resistant to external mechanical wear and damage
- Longer service life

### Delivery:

1-stranded or longer designs, stronger chain diameter, carrying capacities up to 56 t upon request.



<b>Art. no.</b>	<b>77208 618</b>
<b>Brand</b>	RUD
<b>Manufacturer Part Number</b>	25 101000016555
<b>Stop chain design</b>	4 threads
<b>Chain, can be shortened</b>	No
<b>Effective length</b>	2 m
<b>Chain diameter</b>	6 mm
<b>Load-carrying capacity at 0-45° tilt angle</b>	3150 kg
<b>Load-carrying capacity at 45-60° tilt angle</b>	2250 kg
<b>EN standard</b>	818-2
<b>Colour</b>	Pink
<b>Gross Weight</b>	10.140 kg
<b>Product Group</b>	775