

LED Signalleuchte  
 LED signal luminaire


## SIGNALLED II RGB, 1020 mm

Artikel-Nr.:	111090-16
EAN:	4260556624525
Zolltarifnr.:	94054099

Bestellnr.:	111090-16
Modell:	SIGNALLED II RGB
Bauform:	LED Aufbauleuchte
Leuchtmittel:	RGB LED
Lampenleistung Rot:	~10,6 W
Lampenleistung Grün:	~10,6 W
Lampenleistung Blau:	~10,6 W
Lampenlichtstrom Rot:	236 lm
Lampenlichtstrom Grün:	108 lm
Lampenlichtstrom Blau:	372 lm
Lichtverteilung:	direkt
Lichtfarbe:	RGB Farbraum (mindestens 2563 Farben)
Anschlusswert Leuchte:	24V DC - 10% +7% (RGB)
Anschluss Leuchte:	M12 Steckverbinder A-kodiert
Schutzart:	IP54
Schutzklasse:	III
Entblendung:	opalweiß
Abstrahlwinkel:	120°
Betriebstemperatur:	-10... +50 °C
Lampenlebensdauer:	> 60.000 h
Material Gehäuse:	Aluminium
Material Abdeckung:	Polycarbonat
Höhe [B] x Breite [C]:	25 mm x 30 mm
Länge [A]:	1020 mm
Gewicht:	650 g
Bruttogewicht:	1000 g
Risikogruppe:	freie Gruppe
Befestigungszubehör:	2 Paar Halterungen (inkl.)
Dimmbar:	nein
Kennzeichnung:	CE, ETL Listed
Gefertigt in:	Deutschland
Besonderheit:	Signalisieren über Blinken und/oder farbiges Licht



Lampenlebensdauer in Betriebsstunden (L80/B10)

LED Signalleuchte  
LED signal luminaire



**SIGNALLED II RGB, 1020 mm**

<b>Item number:</b>	111090-16
<b>EAN:</b>	4260556624525
<b>Customs tariff number:</b>	94054099

<b>Order number:</b>	111090-16
<b>Model:</b>	SIGNALLED II RGB
<b>Type:</b>	LED surface-mounted luminaire
<b>Illuminant:</b>	RGB LED
<b>Power consumption RED:</b>	~10,6 W
<b>Power consumption GREEN:</b>	~10,6 W
<b>Power consumption BLUE:</b>	~10,6 W
<b>Lamp luminous flux RED:</b>	236 lm
<b>Lamp luminous flux GREEN:</b>	108 lm
<b>Lamp luminous flux BLUE:</b>	372 lm
<b>Light distribution:</b>	direct
<b>Light colour:</b>	RGB colour space (at least 2563 colours)
<b>Connected load:</b>	24V DC - 10% +7% (RGB)
<b>Connection (connector):</b>	M12 A-type encoded
<b>Degree of protection:</b>	IP54
<b>Class of protection:</b>	III
<b>Glare-free</b>	opal white
<b>Beam angle (optics):</b>	120°
<b>Operating temperature:</b>	-10... +50 °C
<b>Lamps lifetime:</b>	> 60,000 h
<b>Housing material:</b>	aluminium
<b>Cover material:</b>	polycarbonate, soft
<b>Height [B] x Width [C]:</b>	25 mm x 30 mm
<b>Length [A]:</b>	1020 mm
<b>Weight (net):</b>	650 g
<b>Gross weight:</b>	1000 g
<b>Risk group (DIN EN 62471):</b>	free group
<b>Mounting accessories:</b>	2 pairs mounting holders (holder for swivel or planar mounting) pin delivery scope
<b>Dimmable:</b>	no
<b>Marking:</b>	CE, ETL Listed
<b>Made in:</b>	Germany
<b>Feature:</b>	Signalling via flashing and/or coloured light



Lamps lifetime in operation hours (L80/B10)