




no. of contacts	performance level			insulator colour	dimensions			
	PL3	PL2	NM30 (S4)		A max.	C	D	E
06	09 18 506 7927	09 18 506 6927	09 18 506 5927	grey	27,22	22,86	12,45	2,54 x 2 = 5,08
10	09 18 510 7927	09 18 510 6927	09 18 510 5927		32,30	27,94	17,53	2,54 x 4 = 10,16
14	09 18 514 7927	09 18 514 6927	09 18 514 5927		37,38	33,02	22,61	2,54 x 6 = 15,24
16	09 18 516 7927	09 18 516 6927	09 18 516 5927		39,92	35,56	25,15	2,54 x 7 = 17,78
20	09 18 520 7927	09 18 520 6927	09 18 520 5927		45,00	40,64	30,23	2,54 x 9 = 22,86
24	09 18 524 7927	09 18 524 6927	09 18 524 5927		50,08	45,72	35,91	2,54 x 11 = 27,94
26	09 18 526 7927	09 18 526 6927	09 18 526 5927		52,62	48,26	37,85	2,54 x 12 = 30,48
30	09 18 530 7927	09 18 530 6927	09 18 530 5927		57,70	53,34	42,93	2,54 x 14 = 35,56
34	09 18 534 7927	09 18 534 6927	09 18 534 5927		62,78	58,42	48,01	2,54 x 16 = 40,64
40	09 18 540 7927	09 18 540 6927	09 18 540 5927		70,40	66,04	55,63	2,54 x 19 = 48,26
50	09 18 550 7927	09 18 550 6927	09 18 550 5927		83,10	78,74	68,33	2,54 x 24 = 60,96
60	09 18 560 7927	09 18 560 6927	09 18 560 5927		95,80	91,44	81,03	2,54 x 29 = 73,66
64	09 18 564 7927	09 18 564 6927	09 18 564 5927		100,88	96,52	86,11	2,54 x 31 = 78,74

	All Dimensions in mm Original Size DIN A3	Scale 1:1	Free size tol.	Ref.
	All rights reserved Department EL PD	Created by STORCK	Inspected by LEHNERT	Standardisation 302077
HARTING D-32339 Espelkamp	Title SEK 18 male STD straight wire wrap without lever 15.0			Doc-Key / ECM-Nr. 100154464/UGD/052/B 500000163153
	Type TB	Number 09185XXX927	Rev. B	Page 2/2