

Life: 20.000 hrs

CRI : ≥ 80

No IR and damaging  
UV radiation

Operating temperature :  
-30°C/+45°C

Beam Angle: 360°

2 years

guarantee 2700K

### Full Glass version

## LED Filament Serie

The decorative lamp filament is back, now in a LED version!

The lamp has a decorative appearance of a conventional lamp  
GLS, Round or Candle.

The lamp is made of the new generation of LED technology. This makes it possible to apply the phosphorus to a filament, instead of a chip. This creates a light emission of 360 °.

Ideal for decorative and functional lighting.



### LED Filament Ball

| Bailey number | Description                                   | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100035103   | LED Filament Ball G45<br>E14 220-240V 1.8W CL | E14  | 1.8       | 180        | A++          |
| 80100035378   | LED Filament Ball G45<br>E14 240V 3W CL       | E14  | 3         | 350        | A++          |
| 80100035104   | LED Filament Ball G45<br>E27 220-240V 1.8W CL | E27  | 1.8       | 180        | A++          |
| 80100035380   | LED Filament Ball G45<br>E27 240V 3W CL       | E27  | 3         | 350        | A++          |



### LED Filament A60

| Bailey number | Description                                | Base | Max. watt | Max. lumen | Energy label |
|---------------|--|------|-----------|------------|--------------|
| 80100035093   | LED Filament GLS A60 E27 220-240V 3W CL    | E27  | 3         | 300        | A++          |
| 80100035094   | LED Filament GLS A60 E27 220-240V 3.5W CL  | E27  | 3.5       | 420        | A++          |
| 80100035095   | LED Filament GLS A60 E27 220-240V 6W CL    | E27  | 6         | 600        | A++          |
| 80100035096   | LED Filament GLS A60 E27 220-240V 7W CL    | E27  | 7         | 690        | A+           |
| 80100035097   | LED Filament GLS A60 E27 220-240V 8.5W CL  | E27  | 8.5       | 850        | A+           |
| 80100035098   | LED Filament GLS A60 B22d 220-240V 3W CL   | B22  | 3         | 300        | A++          |
| 80100035099   | LED Filament GLS A60 B22d 220-240V 3.5W CL | B22  | 3.5       | 420        | A++          |
| 80100035100   | LED Filament GLS A60 B22d 220-240V 6W CL   | B22  | 6         | 600        | A++          |
| 80100035101   | LED Filament GLS A60 B22d 220-240V 7W CL   | B22  | 7         | 690        | A+           |
| 80100035102   | LED Filament GLS A60 B22d 220-240V 8.5W CL | B22  | 8.5       | 850        | A+           |



### LED Filament A60 Top Mirror

| Bailey number | Description                                 | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100035358   | LED Filament GLS A60 E27 240V 4W Top Mirror | E27  | 4         | 350        | A++          |
| 80100035356   | LED Filament GLS A60 E27 240V 6W Top Mirror | E27  | 6         | 500        | A++          |



### LED Filament Candle

| Bailey number | Description                               | Base  | Max. watt | Max. lumen | Energy label |
|---------------|---|-------|-----------|------------|--------------|
| 80100035361   | LED Filament Candle E14 240V 1W CL        | E14   | 1         | 120        | A++          |
| 80100035105   | LED Filament Candle E14 220-240V 1.8W CL  | E14   | 1.8       | 180        | A++          |
| 80100035359   | LED Filament Candle E14 240V 3W CL        | E14   | 3         | 350        | A++          |
| 80100035107   | LED Filament Candle B15d 220-240V 1.8W CL | Ba15d | 1.8       | 180        | A++          |



### LED Filament Cosy

| Bailey number | Description                             | Base  | Max. watt | Max. lumen | Energy label |
|---------------|---|-------|-----------|------------|--------------|
| 80100035364   | LED Filament Cosy E14 240V 1W CL        | E14   | 1         | 120        | A++          |
| 80100035106   | LED Filament Cosy E14 220-240V 1.8W CL  | E14   | 1.8       | 180        | A++          |
| 80100035363   | LED Filament Cosy C35 E14 240V 3W CL    | E14   | 3         | 350        | A++          |
| 80100035108   | LED Filament Cosy B15d 220-240V 1.8W CL | Ba15d | 1.8       | 180        | A++          |



### LED Filament ST64

| Bailey number | Description                      | Base | Max. watt | Max. lumen | Energy label |
|---------------|----------------------------------|------|-----------|------------|--------------|
| 80100035385   | LED Filament ST64 E27 240V 2W CL | E27  | 2         | 220        | A++          |
| 80100035386   | LED Filament ST64 E27 240V 4W CL | E27  | 4         | 450        | A++          |



### LED Filament Globe G95

| Bailey number | Description                      | Base | Max. watt | Max. lumen | Energy label |
|---------------|----------------------------------|------|-----------|------------|--------------|
| 80100035387   | LED Filament Globe G95 E27 2W CL | E27  | 2         | 220        | A++          |
| 80100035388   | LED Filament Globe G95 E27 4W CL | E27  | 4         | 450        | A++          |
| 80100035389   | LED Filament Globe G95 E27 6W CL | E27  | 6         | 720        | A++          |



### LED Filament Globe G125

| Bailey number | Description                       | Base | Max. watt | Max. lumen | Energy label |
|---------------|-----------------------------------|------|-----------|------------|--------------|
| 80100035390   | LED Filament Globe G125 E27 2W CL | E27  | 2         | 220        | A++          |
| 80100035391   | LED Filament Globe G125 E27 4W CL | E27  | 4         | 450        | A++          |
| 80100035392   | LED Filament Globe G125 E27 6W CL | E27  | 6         | 720        | A++          |



### LED Filament Reflector

| Bailey number | Description                        | Base | Max. watt | Max. lumen | Energy label |
|---------------|------------------------------------|------|-----------|------------|--------------|
| 80100035381   | LED Filament R50 E14<br>240V 2W CL | E14  | 2         | 220        | A++          |
| 80100035382   | LED Filament R63 E27<br>240V 4W CL | E27  | 4         | 450        | A++          |
| 80100035384   | LED Filament R80 E27<br>240V 4W CL | E27  | 4         | 450        | A++          |



### LED Filament Pigmy

| Bailey number | Description                               | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100036378   | LED Filament Pigmy E14<br>240V 0.5W 2700K | E14  | 0.5       | 30         | A++          |
| 80100036379   | LED Filament Pigmy E14<br>240V 1W 2700K   | E14  | 1         | 60         | A++          |


## 2500K versions



### LED Filament ST45


| Bailey number | Description                              | Base | Max. watt | Max. lumen | Energy label |
|---------------|--|------|-----------|------------|--------------|
| 80100036394   | LED Filament ST45<br>E27 230V 1.5W 2500K | E27  | 1.5       | 150        | A++          |

## 2200K versions



### LED Filament Colorenta

| Bailey number | Description  | Base | Max. watt | Max. lumen | Energy label |
|---------------|--|------|-----------|------------|--------------|
| 80100035451   | LED Filament<br>Colorenta T30X300<br>E27 5W CL 2200K | E27  | 5         | 550        | A++          |



### LED Filament Tube

| Bailey number | Description                                | Base | Max. watt | Max. lumen | Energy label |
|---------------|--|------|-----------|------------|--------------|
| 80100035631   | LED Filament Tube T20X115 E14 240V 1.5W CL | E14  | 1,5       | 150        | A++          |
| 80100035632   | LED Filament Tube T25X95 E14 240V 1.5W CL  | E14  | 1,5       | 150        | A++          |



### LED Filament Pyramid

| Bailey number | Description                             | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100035456   | LED Filament Pyramid E27 5W Clear 2200K | E27  | 5         | 500        | A++          |
| 80100035704   | LED Filament Pyramid E27 2W Clear 2200K | E27  | 2         | 150        | A++          |
| 80100035705   | LED Filament Pyramid E27 3W Clear 2200K | E27  | 3         | 330        | A++          |



### LED Filament Diamond

| Bailey number | Description                             | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100035706   | LED Filament Diamond E27 2W Clear 2200K | E27  | 2         | 150        | A++          |
| 80100035707   | LED Filament Diamond E27 3W Clear 2200K | E27  | 3         | 330        | A++          |



### LED Filament Twisted

| Bailey number | Description                                       | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100036398   | LED Filament C35 Twisted E14 230V 1.5W 2200K      | E14  | 1.5       | 100        | A++          |
| 80100036399   | LED Filament C35 Twisted E14 230V 3.5W 2200K      | E14  | 3.5       | 200        | A++          |
| 80100036400   | LED Filament C35 Twisted E14 230V 1.5W 2200K Gold | E14  | 1.5       | 100        | A++          |
| 80100036401   | LED Filament C35 Twisted E14 230V 3.5W 2200K Gold | E14  | 3.5       | 200        | A++          |



### LED Filament Ball Top Mirror

| Bailey number | Description                                     | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100036397   | LED Filament G45 E27 230V 3.5W 2200K Top Mirror | E27  | 3.5       | 150        | A++          |

## Dimmable versions 2200K



### LED Filament Long ST64

| Bailey number | Description                                       | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100036362   | LED Long Filament ST64 E27 240V 6W 2200K Dimmable | E27  | 6         | 660        | A++          |




### LED Filament Long Globe

| Bailey number | Description                                       | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100036366   | LED Long Filament G95 E27 240V 6W 2200K Dimmable  | E27  | 6         | 660        | A++          |
| 80100036367   | LED Long Filament G125 E27 240V 8W 2200K Dimmable | E27  | 8         | 800        | A++          |



### LED Filament Wave GLS

| Bailey number | Description                                      | Base | Max. watt | Max. lumen | Energy label |
|---------------|--|------|-----------|------------|--------------|
| 80100036361   | LED Filament Wave A60 E27 240V 6W 2200K Dimmable | E27  | 6         | 600        | A++          |



### LED Filament Wave Candle & Cosy

| Bailey number | Description   | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100036364   | LED Filament Wave C35 E14 240V 3W 2200K Dimmable      | E14  | 3         | 260        | A++          |
| 80100036365   | LED Filament Wave C35 Cosy E14 240V 3W 2200K Dimmable | E14  | 3         | 300        | A++          |



### LED Filament Wave Ball

| Bailey number | Description                                  | Base | Max. watt | Max. lumen | Energy label |
|---------------|--|------|-----------|------------|--------------|
| 80100036360   | LED Filament Wave G45 E27 240V 3W 2200K Dimm | E27  | 3         | 330        | A++          |

### LED Filament Wave Globe


| Bailey number | Description                                   | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100036458   | LED Filament Wave G95 E27 240V 6W 2200K Dimm  | E27  | 6         | 550        | A++          |
| 80100036459   | LED Filament Wave G125 E27 240V 6W 2200K Dimm | E27  | 6         | 550        | A++          |

## Deco versions 1800K



### LED Filament Deco ST64

| Bailey number | Description                                       | Base | Max. watt | Max. lumen | Energy label |
|---------------|---|------|-----------|------------|--------------|
| 80100036119   | LED Filament Deco ST64 E27 240V 2W 1800K Tip      | E27  | 2         | 140        | A++          |
| 80100036120   | LED Filament Deco ST64 E27 240V 2W 1800K Tip Gold | E27  | 2         | 140        | A++          |



### LED Filament Deco Tube

| Bailey number | Description                                      | Base | Max. watt | Max. lumen | Energy label |
|---------------|--|------|-----------|------------|--------------|
| 80100036127   | LED Filament Deco T30X185 E27 240V 2W 1800K      | E27  | 2         | 140        | A++          |
| 80100036128   | LED Filament Deco T30X185 E27 240V 2W 1800K Gold | E27  | 2         | 140        | A++          |



### LED Filament Deco Globe

| Bailey number | Description                                      | Base | Max. watt | Max. lumen | Energy label |
|---------------|--|------|-----------|------------|--------------|
| 80100036121   | LED Filament Deco G80<br>E27 240V 2W 1800K       | E27  | 2         | 140        | A++          |
| 80100036122   | LED Filament Deco G80<br>E27 240V 2W 1800K Gold  | E27  | 2         | 140        | A++          |
| 80100036123   | LED Filament Deco G95<br>E27 240V 2W 1800K       | E27  | 2         | 140        | A++          |
| 80100036124   | LED Filament Deco G95<br>E27 240V 2W 1800K Gold  | E27  | 2         | 140        | A++          |
| 80100036125   | LED Filament Deco<br>G125 E27 240V 2W<br>1800K   | E27  | 2         | 140        | A++          |
| 80100036126   | LED Filament Deco G125<br>E27 240V 2W 1800K Gold | E27  | 2         | 140        | A++          |