

M3.5 Stud Size 48A Yellow Ring Connector Pack of 100

Order code: **33-1200**

Note:

- | | | | | | | | |
|--------------------------------|--|-----|----|----|-----|----|----|
| 1. Maximum electric current: | <table border="1"><tr><td>AWG</td><td>16</td><td>14</td></tr><tr><td>AMP</td><td>18</td><td>30</td></tr></table> | AWG | 16 | 14 | AMP | 18 | 30 |
| AWG | 16 | 14 | | | | | |
| AMP | 18 | 30 | | | | | |
| 2. Maximum electrical rating: | 105°C 600 volts max. | | | | | | |
| 3. Insulation material: | Vinyl | | | | | | |
| 4. Insulator colour: | Blue | | | | | | |
| 5. Terminal material: | Copper | | | | | | |
| 6. Wire range: | 16-14 AWG (1.5-2.5mm ²) | | | | | | |
| 7. Terminal surface treatment: | Tin plated | | | | | | |
| 8. Terminal thickness: | 0.80mm | | | | | | |

