

**Q - MAX PUNCHES    METRIC**

<b>PUNCH SIZE</b>	<b>BOLT SIZE</b>	
10mm	6 m/m x 40	
11mm	6 m/m x 40	
12.7mm	8 m/m x 40	
14mm	8 m/m x 40	
15mm	8 m/m x 30	
16mm	8 m/m x 30	
17.5mm	8 m/m x 30	
18.6mm	10 m/m x 35	
19mm	10 m/m x 35	
20mm	10 m/m x 35	
20.4mm	10 m/m x 35	
21mm	10 m/m x 35	
22.5mm	10 m/m x 45	
24mm	10 m/m x 45	
25mm	10 m/m x 45	
27.5mm	10 m/m x 45	
28.3mm	10 m/m x 45	
29mm	10 m/m x 45	
30mm	10 m/m x 45	
31mm	10 m/m x 45	
32.5mm	12 m/m x 45	
34mm	12 m/m x 45	
35mm	12 m/m x 45	
37mm	12 m/m x 50	
37.5mm	12 m/m x 50	
40mm	12 m/m x 50	
45mm	12 m/m x 50	
47mm	12 m/m x 50	
48mm	12 m/m x 50	
50mm	12 m/m x 50	
51mm	12 m/m x 50	
52mm	16 m/m x 60	
54mm	16 m/m x 60	
55mm	16 m/m x 60	
60mm	16 m/m x 60	
64mm	16 m/m x 65	
65mm	16 m/m x 65	
70mm	16 m/m x 65	
75mm	16 m/m x 65	
76.5mm	16 m/m x 70	
80mm	16 m/m x 70	

