

## Connection cable for Interroll Motor Rollers, snap-in



Art. no.	BW2755	BW3030
<b>Specifications</b>		
Pole number	5	
Connection	1:1	
Cable length	2 m	1,2 m
<b>Electrical data connector</b>		
Rated current	2 x 4 A (Pin 1 + 3) at 40 °C 3 x 1 A (Pin 2 + 4 + 5)	
Rated voltage	60 V	
Pole number	5	
Insulation resistance	≥ 100 MΩ	
<b>General specific values connector</b>		
Protection class	IP67 when mated and locked	
Contact material	CuZn	
Contact surface material	Ni, Au gal.	
Material handle	TPU, UL 94, black	
<b>Specific values cable</b>		
Cable type	TPU black	
Conductor cross-section	2 x 0,34 mm <sup>2</sup> , 3 x 0,14 mm <sup>2</sup>	
Core colors	brown, white, blue, black, gray	

### Pin assignment

