



| | | | |
|---|------------|------------------------|---|
| C-TRU PROCESS EQUIPMENTS 53, Satyam Ind. Estate, Subhash Road, Jogeshwari (E), Mumbai 400060 INDIA | Data Sheet | Data Sheet No : 01-008 |  |
| | | Revision : 00 | |
| | | Page : 1 of 1 | |
| “ARSEN” Model 920-F Plain Type Double Window Sight Flow Indicator | | | |



APPLICATIONS : Where no internal indication is required the Model 920-F is ideal when observing colour and clarity hold precedence over verifying flow.

OPERATING CONDITIONS:

Max Operating Pressure : 52 bar

Max Operating Temperature : 150°C – Sodalime Glass, 280°C – Borosilicate Glass

OPTIONS :

- 150 # - 300 #
- With Light Fittings
- PN 16 to PN 40
- With Anti-Frost Windows
- BS 10 Table 'F'

CERTIFICATIONS : EN 10204 3.1B

STANDARD DIMENSIONS:

| Size | 15 | 20 | 25 | 40 | 50 | 65 | 80 | 100 | 150 | 200-300 |
|-------|-----|-----|-----|-----|-----|-----|-----|-----|-----|----------------|
| A ± 5 | 130 | 150 | 160 | 200 | 230 | 290 | 310 | 350 | 480 | ON |
| B Ø | 25 | 45 | 45 | 63 | 80 | 100 | 100 | 125 | 175 | Request |

DIMENSIONS ARE NOT FOR CONSTRUCTION UNLESS CERTIFIED

MATERIALS OF CONSTRUCTION :

| Part No | Part Name | Standard Material | | |
|---------|-------------|--|--|----------------|
| 1 | Body | A 216 Gr. WCB | A 351 Gr. CF8 | A 351 Gr. CF8M |
| 2 | Cover Plate | A 216 Gr. WCB | A 351 Gr. CF8 | A 351 Gr. CF8M |
| 3 | Glass | Toughened Sodalime B S 3463 Max Temperature 150°C | | |
| | | Toughened Borosilicate DIN 7080 Max Temperature 280°C – Ilmadur make | | |
| 4 | Sealing | CAF / Aramid | PTFE | |
| 5 | Cushion | CAF / Aramid (Non- Asbestos) | | |
| 6 | Bolt Nuts | Zinc Plated 4.6/ 4 | A 2 70 | |
| | Finish | Ultramarine Blue RAL 5002 to suit 250°C | Electro-polished for enhanced corrosion resistance | |

Note: Also available in Cast Iron & Ductile Iron. Optional Materials will be provided on request

| | | | |
|--|-------------------------------|---------------------------------|--|
| Fully PED Compliant | | CE Marked where Relevant | |
| PRODUCTS / SERVICES ARE SOLD SUBJECT TO COMMERCIAL TERMS ON OUR WEBSITE | | | |
| C-TRU PRODUCT RANGE | | | |
| “LEVELTROL” Liquid Level Gauges | “ARSEN” Sight Flow Indicators | “FLOCLEAN” Strainers | |
| “LEVELTROL” Liquid Level Switches | “ARSEN” Flush Bottom Valves | Toughened Borosilicate Glasses | |
| ‘ARSEN’ – CLEARLY THE √ CHOICE | | | |
| Tel: +91-22-32963546/65081035, Fax: +91-22-28361150 E mail: sales@arsen-india.com Website: www.arsen-india.com | | | |