

Pneumatic belt sander RRG-36 17K

10x330/6x330mm



Application:

For surface grinding in metal and wood processing as well as for deburring in hard-to-reach areas.

Execution:

- With safety trigger
- With sound-proofed air outlet
- With adjustable sound insulation

Delivery:

With sanding arm 6x330mm and 10x330mm



Art. no.	75066 020
Brand	RED ROOSTER
Manufacturer Part Number	RRG-36 17K
Model	RRG-36 17K
Valve design	Lever valve
Max. idle speed	20000 rpm
Power input	280 W
Air consumption	6.7 l/s
Sound-pressure level	80 dB
Connection thread	1/4 inch
Length	265 mm
Inner hose diameter	10 mm
Min. sanding belt width	6 mm
Max. sanding belt width	10 mm
Weight	0.75 kg
Grinding belt length	330 mm
Gross Weight	0.788 kg
Product Group	7AE

EAN

8717981049899

