








# Cabinets – Varistar CP Electronics

**EXTERIOR MOUNTING    STEEL DOORS PERFORATED**
**ORDER INFORMATION**

		Steel doors perforated			Double steel door perforated	Handle with round cylinder	Handle for DIN profile half cylinder	Grounding Kit
		handle with 1 point locking	handle with 1 point locking	handle with 3 points locking	handle with 3 points locking			
 <p>Completely in RAL 7021 (black grey)</p>		 <p>Door St, 1.5 mm, perforated, 180° hinge, lever handle without lever, 2 keys</p> <p>Please order GND/earthing kit separately</p>	 <p>Door St, 1.5 mm, perforated, 180° hinge, lever handle with key insert, 2 keys.</p> <p>Please order GND/earthing kit separately</p>	 <p>Door St, 1.5 mm, perforated, 180° hinge, lever handle with key insert, 2 keys.</p> <p>Please order GND/earthing kit separately</p>	 <p>Double door St, 1.5 mm, perforated, 180° hinge, lever handle with key insert, 2 keys.</p> <p>Please order GND/earthing kit separately</p>	 <p>Handle with round cylinder</p>	 <p>Lever handle for 3 point locking</p>	<p>Please order one grounding kit per cabinet frame.</p> <p>The kit is sufficient to ground all components of the cabinet.</p>
No.	Cabinet dimensions			PU 1 piece assembled	PU 1 piece assembled	PU 1 piece assembled	PU 1 piece assembled	PU 1 piece assembled
	Height U	Width mm	Depth mm					
	<b>Completely in RAL 7021</b>			<b>RAL 7021</b>	<b>RAL 7021</b>	<b>RAL 7021</b>	<b>RAL 7021</b>	
1	24	1200	600	600	21630-507	21630-408	21630-424	21630-448
2	24	1200	600	800	21630-507	21630-408	21630-424	21630-448
3	29	1400	600	600	21630-509	21630-410	21630-426	21630-450
4	29	1400	600	800	21630-509	21630-410	21630-426	21630-450
5	33	1600	600	600	21630-511	21630-412	21630-428	21630-452
6	33	1600	600	800	21630-511	21630-412	21630-428	21630-452
7	38	1800	600	600	21630-513	21630-414	21630-430	21630-454
8	38	1800	600	800	21630-513	21630-414	21630-430	21630-454
9	38	1800	800	600	21630-514	21630-415	21630-431	21630-455
10	42	2000	600	300	21630-515	21630-006	21630-098	21630-020
11	42	2000	600	600	21630-515	21630-006	21630-098	21630-020
12	42	2000	600	800	21630-515	21630-006	21630-098	21630-020
13	42	2000	800	600	21630-516	21630-013	21630-101	21630-027
14	42	2000	800	800	21630-516	21630-013	21630-101	21630-027
15	47	2200	600	300	21630-517	21630-007	21630-099	21630-021
16	47	2200	600	600	21630-517	21630-007	21630-099	21630-021
17	47	2200	600	800	21630-517	21630-007	21630-099	21630-021
18	47	2200	800	600	21630-518	21630-014	21630-102	21630-028
19	47	2200	800	800	21630-518	21630-014	21630-102	21630-028

**Other handles**

Lever handle ASSA cylinder for 3 point locking (without cylinder)	<b>24630-062</b>
Lever handle KABA cylinder for 3 point locking (without cylinder)	<b>24630-063</b>

**DIN profile half cylinder**

A) DIN profile half cylinder, key no. 333, qty = 1	<b>60114-121</b>
B) DIN profile half cylinder, push button lockable by keys, Key no. 2233, qty = 1	<b>23130-601</b>

