



BE-8725S - BE-8708S
**ERGO™ VDE Insulated Hex Socket-
Head Screwdrivers with 3-
Component Handle 2.5 mm-8 mm**



PRODUCT DETAILS







- Screwdriver developed according to the scientific ERGO™ process
- ERGO™ insulated VDE screwdriver for hexagonal head screws
- Phosphate finish tip for higher accuracy
- three-component handle for maximum user comfort, soft material with ridged surface provides superior grip and greater force transmission
- Maximum comfort with minimum effort due to the ergonomic design
- Easy to choose the right tip with the colour-coded handle and permanent symbol on the domed end
- Integrated hanging hole
- Anti-roll flat face on handle
- High-performance alloy steel, insulation moulded directly onto blade
- For work on live equipment up to 1000 V
- Individually inspected and manufactured according to IEC 60900, tested in a water bath at 10000 V
- IEC 60900, VDE certified



Follow the Fish!



PRODUCT ATTRIBUTES

Product						
BE-8725S	2.5 mm	100 mm	20 mm	122 mm	222 mm	33 g
BE-8703S	3 mm	125 mm	20 mm	122 mm	247 mm	62 g
BE-8704S	4 mm	150 mm	20 mm	122 mm	272 mm	78 g
BE-8705S	5 mm	175 mm	27 mm	122 mm	297 mm	128 g
BE-8706S	6 mm	150 mm	27 mm	122 mm	272 mm	159 g
BE-8708S	8 mm	200 mm	36 mm	122 mm	322 mm	235 g

