

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0579649702](#)
Status: **Active**
Description: 1.52mm OBD-II Male Terminal for AVS(CAVS) 0.3-0.5

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-57964-001-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	57964
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Product Name	OBD-II
UPC	756054300091

Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.306/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.60-1.40mm
Wire Size AWG	20, 22
Wire Size mm ²	0.30-0.50

Material Info

Reference - Drawing Numbers

Crimp Specification	CS-57964-001-002
Packaging Specification	PK-57964-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[57964](#) Series

Use With

[685031602](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
-------------	-----------

Extraction Tool for MTC (Multi Terminal Connector) Female Terminal, 14-18 AWG	638138600
---	---------------------------

Hand Crimp Tool for OBD II 1.52mm Crimp Terminal, 0.30-0.50mm ² and 20-22 AWG	638194700
--	---------------------------

FineAdjust Applicator 639011200
for 1.52mm Female
Terminal
T2 Terminator for 639111200
OBD II 1.52mm
Crimp Terminal for
20-22 AWG

This document was generated on 02/04/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION