



MODEL	VOLTAGE		NO LOAD		AT MAXIMUM EFFICIENCY				STARTING		max. OUTPUT POWER W	POLES	CAPACITOR	BRUSHES
	Operating Range	Nominal	Speed	Current	Speed	Current	Torque	Output Power	Current	Torque				
	VDC	VDC	rpm	A	rpm	A	mNm	W	A	mNm				
FK285-15110S-57H	10,0-16,0	14,0	12.203	0,06	10.220	0,31	3,18	2,79	1,58	19,56	5,13	5	none	carbon



**DIRECTION OF ROTATION**



Irrtum und Druckfehler vorbehalten / Errors and Omissions excepted