

INOVA[®] XP[™]

HIGH-POWERED LED FLASHLIGHT




Featuring the convenience of a pen light and the performance of a serious LED flashlight, you will never be without powerful illumination again.

With its precision-machined aluminum body and stainless steel clip, the INOVA XP LED Pen Light is designed to fit comfortably in your pocket and be securely carried wherever you go. Sleek and compact, yet rugged enough to withstand serious use, its patented optical system, featuring a uniform focused spot with flood beam pattern, provides up to 144 lumens of super bright white light, with an effective range of 249 feet. Its dual-mode functionality provides long hours of either High or Low power light output, as well as a battery-saving lock-out mode. Impact and water-resistant, the INOVA XP is powered by 2-AAA alkaline batteries (included).

FEATURES:

- ▶ Dual Light Mode Functionality. Features both HIGH and LOW Light Output Modes
- ▶ LED Color: White
- ▶ Available with a Black Anodized finish
- ▶ Lumens: High - 144 | Low - 30
- ▶ Run Time: High 1 hour | Low 34 hours
- ▶ Battery Type: 2-AAA Alkaline batteries included
- ▶ Effective Range: 249 ft (76 m)
- ▶ High-Powered, energy efficient 38,900 hr LED
- ▶ Patented optical system - precision machined aluminum reflector with thermal management interface
- ▶ Aerospace-grade aluminum with high grade anodized finishes
- ▶ Features replaceable stainless steel clip
- ▶ Shockproof, Crushproof, Water-Resistant Construction with O-Ring seals
- ▶ 3 Position End-Cap Switch activates constant and momentary high and low as well as a lockout mode
- ▶ Customization Available - Engrave your logo or company name. [Click Here for more information](#)
- ▶ Dimensions: 4.64" x 0.78" | 11.87 cm x 1.98 cm
- ▶ Weight: 1.94 oz. | 55.00 g
- ▶ Try me packaging - allows for lighting demonstration
- ▶ Limited Lifetime Warranty USA



Anodized threads provide durability and protection from the elements.



Patented 3 position end-cap switch activates constant and momentary HIGH and LOW power modes and Lockout mode.



Retail Packaging Dimensions:
 3.7" W x 7.5" H x 0.7" D
 94 mm W x 190.5 mm H x 19.8 mm D

ANSI/NEMA FL1 STANDARDS

LIGHT OUTPUT HIGH 144 LUMENS LOW 30 LUMENS	RUN TIME HIGH 1 H LOW 34 H	WATER RESISTANCE IPX4	IMPACT RESISTANCE 1m	RANGE 76m
---	---	---------------------------------	--------------------------------	---------------------

INOVA, XS, X1, X2, X03, X5, X3R, X3A, T1, T2, T3, T3R, T4R, T5 and RADIANT are registered trademarks of Nite Ize, Inc. The distinctive shapes, styles, packaging, configuration and overall appearance of all INOVA[®] flashlights and products are trademarks of Nite Ize, Inc. The unique bulb configurations and barrel shapes inherently identify them as members of the quality family of INOVA[®] brand products.