



Temperature Sensors

Thermoresistances


► (RTS) Bayonet Bore Type with Silicone Cable



► (RTST) Bayonet Bore Type with Teflon Cable



► (RTSM) Bayonet Bore Type with Braided Wire Cable



► (RTSKP5) Bayonet Type with Cable Lug



- Max. operating temperature** : 400°C for Braided wire, 200°C for Silicone, 260°C for Teflon
- Standard cable types** : Fiber glass + Fiber glass + Braided wire, 3x0,22 mm² / Silicone + Silicone, 3x0,22 mm² / Teflon + Teflon, 3x0,22 mm²
- Standard cable length (K)** : K01 = 1mt, K02 = 2mt, K03 = 3 mt, K04 = 4mt, K05 = 5 mt.
- Sensor type** : DIN/EN60751 Class "B" 1xPt-100 for E=1 or 2xPt-100 for E=2
- Protection tube material** : AISI304 (DIN1.4301), AISI316 Order Code "316"