


CUBE20S POTENTIAL DISTRIBUTORS

4 x 24 V DC + 4 x 0 V DC

Potential distributor
Expansion module
4 x 24 V DC[Link to Product](#)**Illustration**

Product may differ from Image

Approvals


General data

Protection	IP20
Connection	Spring clamp terminals: 0.08...2.5 mm ² (AWG 28...12)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -25...+70 °C)
Dimensions H × W × D	109×12.9×52.5 mm

Module Supply

Operating voltage	max. 30 V DC
Total current	max. 10 A

Commercial data

country of origin	TH
customs tariff number	85369010
minimum order quantity	1