



CAL IIS

Model Number


V1S-W-BK

Male cordset, M12, 4-pin, field attachable

Features

- · Screw terminal connection
- Metal locking

Dimensions



General specifications	
Number of pins	
0	

Technical data

Male connector Connection 1 Construction type 1 right angle M12 Threading 1 UL File Number E363587

Electrical specifications

Operating voltage max. 250 V AC/DC Operating current max. 4 A Volume resistance < 8 mΩ

Ambient conditions

Ambient temperature -40 ... 85 °C (-40 ... 185 °F)

Pollution Degree 3

Mechanical specifications

Degree of protection

1 x M12 right-angled connector Screw terminals for max. 0.75 mm² , AWG 18 Connection

Material CuZn Contacts Contact surface CuSnZn CuZn Connector

PBT, black Body Cable

Sheath diameter 4 ... 6 mm Mating cycles 50

Compliance with standards and directives

Standard conformity Degree of protection EN 60529:2000

Electrical connection

