


Product description

Swap medium for activating iFeatures for SCALANCE W in Access Point and Client Mode and for simple device replacement in the event of a fault
 KEY-PLUG W780, REPLACEABLE MEDIUM FOR ACTIVATING OF IFEATURES FOR SCALANCE W IN ACCESS POINT AND CLIENT MODE AND FOR EASY REPLACEMENT OF DEVICE IN CASE OF FAILURE, AND FOR STORAGE OF CONFIGURATION DATA.



Suitability for use

Activation of iFeatures iPCF, iPCF-MC, iREF

Permitted ambient conditions

Ambient temperature

- during operation 0 ... 60 °C
- during storage -40 ... +80 °C
- during transport -40 ... +80 °C

Relative humidity / at 25 °C / without condensation / during operation / maximum 95 %

Protection class IP 20

Design, dimensions and weight

Width 24.3 mm

Height 17 mm

Depth 8.1 mm

Net weight 5 g

design of the removable storage / C-PLUG No

design of the removable storage / KEY-PLUG Yes

Product properties, functions, components / general

Storage capacity 256 Mibyte

Further Information / Internet Links

Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL <http://www.siemens.com/snst>

- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09.03.2015