

ABS 3819 13 G



Sample image

Order symbol: ABS 3819 13 G

Product nbr: 5880361

Description: Enclosure. ABS



Remarks: Opaque cover

Including: Base with screws for mounting plate. cover with PUR gasket and polyamide cover screws.

EAN: 6418074039040

El. number:

- Finland: 3423759
- Denmark:
- Sweden: 2539713



| Dimensions: | Height | Width | Depth |
|-------------|--------|-------|-------|
| mm: | 380 | 190 | 130 |
| inch: | 14.96 | 7.48 | 5.12 |

Materials:

| | |
|------------------|----------------------|
| Material: | ABS |
| Base colour: | RAL 7035 -light grey |
| Cover colour: | RAL 7035 -light grey |
| Gasket material: | Polyurethane |

Temperatures:

| | |
|-------------------------------|-------------|
| Temperature °C (short term):: | -40 ... 80 |
| Temperature °C (continuous): | -40 ... 60 |
| Temperature °F (short term): | -40 ... 175 |

Accessories:

| | |
|--------|---|
| EKMZR | Extension frame. for enclosures: (380 x 190 x 50) |
| EKV 12 | DIN-35 Mounting rail. for enclosures: (160 x 35 x 1) |
| EKV 32 | DIN-35 Mounting rail. for enclosures: (335 x 35 x 1) |
| EKMVT | Back Panel. for enclosures: (338 x 148 x 1) |

Rating:

| | |
|--|-------------------|
| Ingress protection (EN 60529): | IP66; IP67; |
| Impact Resistance (EN 62262): | IK08; |
| Electrical insulation: | Totally insulated |
| Halogen free (DIN/VDE 0472, Part 815): | 1 |
| UV resistance: | - |
| Flammability Rating: | UL 94 HB |

Temperature °F (continuous):

-40 ... 140

Glow Wire Test (IEC 695-2-1) °C:

650 °C

NEMA Class

Certificates:

Certificate NCS FI 30308