

PNOZ m EF Multi Link

772120



Configurable control system PNOZmulti 2 expansion module Safe connection.

Technical details

Approvals:	CE;cULus Listed;TÜV;BG;CCC
Max. data transmission time:	5 ms
Supply voltage (V):	24,0
Supply voltage type:	DC
Power consumption DC:	2.5 W
Terminal style:	Plug-in
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	120.0 mm
Gross weight:	113 g
Net weight:	91 g
Ambient temperature:	0 - 60 °C

Accessories



783538

Spring terminals PNOZ mmc2p, mml1p 1 pc.



793538

Screw terminals PNOZ mmc2p, mml1p 1 pc.

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)



793539

Screw terminals PNOZ mmc2p,mml1p 10 pcs.



783539

Spring terminals PNOZ mmc2p,mml1p 10 pcs