





Material: Messing vernickelt  
 max. Betriebsdruck: 18 bar  
 max. Betriebstemperatur: 200 °C  
 verwendbare Schläuche: PA, PE, PU



13.800-8-E

### Winkelverbinder

Typen Nr.	Artikel Nr.	ØD	L	 1	 2	 3	O-Ring
13.800-6-E	115239	6/4	21,5	12	8	12	ohne
13.800-8-E	115240	8/6	22,5	14	10	14	ohne
13.800-10-E	115238	10/8	25,5	16	11	16	ohne