


**ART.: 8425463173410**

AS425 LED MEDIUM REFLECTOR



Art.: 8425463173410, AS425 LED, 20W, 4000K, Driver static, Direct / medium (2 x 11°-22°), White, LED track light for interior, including: Extruded aluminum profile and die-cast aluminum spotlight housing, powder-coated, Tilting and turning spotlight head, High-brilliance spherical faceted reflector for maximum lamp performance and neutral colour rendering, Bayonet-closure ring for a toolless replacement of the reflector and the louvre, Reflector in Medium design, Colour rendering index Ra > 90, Colour tolerance according to MacAdam ≤ 3 SDCM Universal tri-phase adaptor included, Complete with electric converter, Toolless mounting, Complete with clear safety glass pane

<b>Connected load</b>	20 W
<b>Luminous flux</b>	2250 lm
<b>Efficiency</b>	112 lm/W
<b>Colour temperature</b>	4000K
<b>Colour rendering (CRI)</b>	80
<b>IP class</b>	20
<b>Nominal voltage</b>	220 – 240 V
<b>Colour</b>	RAL 9010

