

Forked clamps

With round clamping face



Version:

- Heat-treated steel
- Painted
- With round clamping face



Art. no.	26130 040
Slot width	14 mm
Length	160 mm
Suitable cheese-head screw DIN 912	M12, M14
Clamping shoe height	25 mm
Clamping shoe width	40 mm
Diameter	20 mm
Length 2	45 mm
Length 3	30 mm
DIN	6315

EAN-Code

4020772070724