

Adjustable clamps

Short and infinitely adjustable with U-piece



Application:

For clamping workpieces.

Version:

- With U-piece
- Suitable for tough conditions, e.g. on presses
- Tempered
- Galvanised and blue passivated
- Infinitely adjustable

Delivery:

With U-piece, though without clamping screw



Art. no.	26225 040
For table grooves according to DIN 650	24 mm, 28 mm
Min./max. clamping height	0-75 mm
Min./max. clamping height 2	54-111 mm
Clamping shoe length	174 mm
Clamping shoe width	76 mm
Bore diameter	26 mm
Distance 2	100 mm
Distance	39 mm
Distance 1	52 mm
Distance 3	24 mm
Suitable screw DIN 787	M24 x 200 mm
Slot nut width of clamping screw	24 mm, 28 mm
Height	111 mm

EAN-Code

402077207396 1