

**C.A 732
C.A 703
C.A 702**

**CONTACT-FREE AC VOLTAGE
DETECTOR **C.A 732****

TORCH FUNCTION

- Phase/neutral identification
- IEC 61010 1000 V Cat III
- Double insulation



BUILT-IN TORCH:

lets you test your outlets and cables... even with poor lighting, and locate an electrical panel and any open circuit-breakers in the dark!

ULTRA-SIMPLE TO USE
The tip of the instrument lights in the presence of 230 V, 50/60 Hz AC

DESIGNED FOR CONVENIENCE
With its pen shape and clip, you can keep it in a pocket, ready for use at all times. In addition, the moulded body provides an outstandingly firm and comfortable grip.



**POCKET DIGITAL MULTIMETERS
C.A 702 and **C.A 703****

CONTACT-FREE VOLTAGE DETECTION

- AC and DC voltages
- Resistance
- Continuity and diode tests
- Current (C.A 703)
- IEC 61010 600 V CAT IV

TORCH FUNCTION



SAFETY IN ALL SITUATIONS
Thanks to their small size and built-in probe tips, you can take them with you everywhere.

Safety in all situations for a diagnostic tool that is always available.

IEC 61010
600 V CAT IV / 1000 V CAT III



CHARACTERISTICS

	C.A 702	C.A 703
V DC / precision	200 mV / $\pm 0.5\%$ L + 3 D 2.000 V; 20.00 V; 200.0 V; 600 V / $\pm 1.2\%$ L + 3 D > 600 V / outside specification	
V AC / precision (40-400 Hz)	2.000 V; 20.00 V / $\pm 1.0\%$ L + 8 D 200.0 V; 600 V / $\pm 2.3\%$ L + 10 D > 600 V / outside specification	
I DC / precision	200.0 μ A; 2000 μ A / $\pm 2.0\%$ L + 8 D 20.00 mA; 200.0 mA / $\pm 2.0\%$ L + 8 D 200 mA / 500 V electronic fuse	
I AC / precision	200.0 μ A; 2000 μ A / $\pm 2.5\%$ L + 10 D 20.00 mA; 200.0 mA / $\pm 2.5\%$ L + 10 D 200 mA / 500 V electronic fuse	
Resistance / precision	200.0 Ω / $\pm 0.8\%$ L + 5 D 2.000 k Ω . 20.00 k Ω . 200.0 k Ω / $\pm 1.2\%$ L + 5 D 2.000 M Ω / $\pm 5.0\%$ L + 5 D 20.00 M Ω / $\pm 10.0\%$ L + 5 D 600 V rms	
Diode test Test alarm Protection	1.999 V $V_{Test} \leq 1.5$ V $I_{Test} \leq 1.5$ A 600 V rms	
Continuity sound test Buzzer Protection	199.9 Ω R < approx. 60 Ω 600 V rms	



- **C.A 732**
(176 x 26 mm - 48 g):
supplied in blister
pack with 2 x 1.5 V
AAA batteries and
operating manual.

- **C.A 702 and C.A 703** (104 x 55 x 32.5 mm - 145 g):
supplied in blister pack with 2 cords with probe tips,
2 x 1.5 V AAA batteries, and operating manual.

To order:

- **C.A 702** P01191739Z
- **C.A 703** P01191740Z
- **C.A 732** P01191745Z
- **200 x 100 x 40 carrying case** P01298065Z

YOUR DISTRIBUTOR

FRANCE
Chauvin Arnoux
190, rue Championnet
75876 PARIS Cedex 18
Tel: +33 1 44 85 44 38
Fax: +33 1 46 27 95 59
export@chauvin-arnoux.fr
www.chauvin-arnoux.fr

UNITED KINGDOM
Chauvin Arnoux Ltd
Unit 1 Nelson Ct, Flagship Sq, Shaw Cross Business Pk
Dewsbury, West Yorkshire - WF12 7TH
Tel: +44 1924 460 494
Fax: +44 1924 455 328
info@chauvin-arnoux.co.uk
www.chauvin-arnoux.com

MIDDLE EAST
Chauvin Arnoux Middle East
P.O. BOX 60-154
1241 2020 JAL EL DIB - LEBANON
Tel: +961 1 890 425
Fax: +961 1 890 424
camie@chauvin-arnoux.com
www.chauvin-arnoux.com

 **CHAUVIN
ARNOUX**
GROUP