

# Crimp Fittings

# Press-armaturen


# Embouts sertis

# Raccordi a graffare

# Racores para presión

## DS


DKO Female Swivel, Heavy Duty  
 Dichtkopf DKOS, schwere Baureihe  
 DKO série S  
 Femmina girevole DKOS, serie pesante  
 Hembra loca DKOS, serie pesada



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G5DS3	1S5DS3	1A5DS3	M16x1,5		8	5	-3	43,4	25,9		2,5	19		
	1S3DS4		M14x1,5		6	6	-4	44,9	21,5		4,2	17		
1G5DS4	1S5DS4	1A5DS4	M16x1,5		8	6	-4	49,5	26,1		4,2	19		
1G6DS4	1S6DS4	1A6DS4	M18x1,5		10	6	-4	50,8	27,4		4,2	22		
1G6DS5	1S6DS5	1A6DS5	M18x1,5		10	8	-5	51,4	27,4		5,3	22		
1G8DS5	1S8DS5	1A8DS5	M20x1,5		12	8	-5	51,6	27,7		5,3	24		
1G8DS6	1S8DS6	1A8DS6	M20x1,5		12	10	-6	53,8	28,5		6,7	24		
1G10DS6	1S10DS6	1A10DS6	M22x1,5		14	10	-6	56,9	31,6		6,7	27		
1G10DS8	1S10DS8	1A10DS8	M22x1,5		14	12	-8	55,2	25,5		9,6	27		
1G12DS8	1S12DS8	1A12DS8	M24x1,5		16	12	-8	62,4	32,7		9,6	30		
1G16DS10	1S16DS10	1A16DS10	M30x2,0		20	16	-10	66,9	37,5		12,8	36		
1G20DS12	1S20DS12	1A20DS12	M36x2,0		25	19	-12	72,0	41,6		15,5	46		
1G25DS16	1S25DS16	1A25DS16	M42x2,0		30	25	-16	78,5	44,1		20,7	50		
1G32DS20	1S32DS20	1AP32DS20*	M52x2,0		38	31	-20	93,7	49,7		26,6	60		
		1AT32DS20**	M52x2,0		38	31	-20	93,7	49,7		26,6	60		

## DSA

DKO Female Swivel, Heavy Duty, 45° Elbow  
 Dichtkopf DKOS, schwere Baureihe, 45° Krümmer  
 DKO série S coudé 45°  
 Femmina girevole DKOS a 45°, serie pesante  
 Hembra loca DKOS acodado a 45°, serie pesada



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting						mm	mm	mm	mm			mm
1G5DSA3	1S5DSA3	1A5DSA3	M12x1,5		8	5	-3	53,5	36,0	16,0	2,5	19		
1G6DSA4	1S6DSA4	1A6DSA4	M14x1,5		10	6	-4	61,4	38,0	17,0	4,2	22		
1G8DSA5	1S8DSA5	1A8DSA5	M16x1,5		12	8	-5	62,9	39,0	18,5	5,3	24		
1G8DSA6	1S8DSA6	1A8DSA6	M16x1,5		12	10	-6	68,3	43,0	19,0	6,7	24		
1G10DSA6	1S10DSA6	1A10DSA6	M18x1,5		14	10	-6	68,8	43,5	20,0	6,7	27		
1G12DSA8	1S12DSA8	1A12DSA8	M22x1,5		16	12	-8	79,7	50,0	23,0	9,6	30		
1G16DSA10	1S16DSA10	1A16DSA10	M26x1,5		20	16	-10	89,3	59,9	26,0	12,8	36		
1G20DSA12	1S20DSA12	1A20DSA12	M30x2,0		25	19	-12	107,4	77,2	32,5	15,5	46		
1G25DSA16	1S25DSA16	1A25DSA16	M36x2,0		30	25	-16	121,4	87,0	37,5	20,7	50		
1G32DSA20	1S32DSA20	1AP32DSA20*	M45x2,0		38	31	-20	166,5	122,9	45,9	26,6	60		
		1AT32DSA20**	M45x2,0		38	31	-20	166,9	122,9	45,9	26,6	60		

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire

\* 1-wire  
 \*\* 2-wire