

## MSUD VALVE PLUG FORM A ,CAPACITY REDUCER -40%

PUR 3X0.75 black UL/CSA, drag ch 1.5m

Power reducer (40 %)  
Valve Connectors  
Form A (18 mm)  
24 V DC  
LED (yellow)

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Form

18211

#### Technical Data

|                               |  |
|-------------------------------|--|
| Operating voltage             | 21.6...26.4 V DC                                       |
| Operating current per contact | max. 5 A   |
| Locking of ports              | M3 (recommended torque 0.4 Nm)                         |
| Protection                    | IP65 and IP67 when plugged and screwed down (EN 60529) |
| Housing                       | Black plastic (gray on request)                        |
| Frequency                     | max. 1 Hz  |
| Switching time                | max. 200 ms  |
| Operating frequency           | 300...500 Hz   |

#### Cables

|                       |                          |
|-----------------------|--------------------------|
| Cable number          | 636                      |
| No./diameter of wires | 3 × 0.75 mm <sup>2</sup> |

|                             |                                 |
|-----------------------------|---------------------------------|
| Wire isolation              | PP (bk, num, gnye)              |
| C-track properties          | 5 Mio.                          |
| Torsion                     | 2 Mio. $\pm$ 180°/m             |
| Jacket Color                | black                           |
| Shore hardness outer jacket | 90 $\pm$ 5A                     |
| Material (jacket)           | PUR (UL/CSA)                    |
| Outer diameter              | approx. 5.9 mm                  |
| Bend radius (fixed)         | 5 $\times$ outer $\varnothing$  |
| Bend radius (moving)        | 10 $\times$ outer $\varnothing$ |
| Temperature range (fixed)   | -40...+80 °C                    |
| Temperature range (mobile)  | -25...+80 °C                    |

#### Commercial data

|                        |          |
|------------------------|----------|
| country of origin      | CZ       |
| customs tariff number  | 85444290 |
| minimum order quantity | 1        |