


## M12 FEMALE FLANGE PLUG C CODED FRONT MOUNT

PP-wires 3X0.75 0.2m

Flange M12 female  
3-pole  
Front mounting  
with multi-strand wire

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Form

20221

#### Technical Data

Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 x 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

#### Cables

Cable number	930
No./diameter of wires	3 x 0.75 mm <sup>2</sup>
Wire isolation	PP (bk, num, gnye)
Shore hardness outer jacket	90 ± 5A

Outer diameter	approx. 1.85 mm
Bend radius (fixed)	5 × outer Ø
Bend radius (moving)	10 × outer Ø
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

**General data**

Temperature range	-25...+85 °C
-------------------	--------------

**Commercial data**

country of origin	DE
customs tariff number	85444290
minimum order quantity	1