



Datenblatt - Fiche technique - Data sheet

**11.04.5253**




ROLINE VGA-Kabel HD15 ST - ST mit Ferritkern, 3,0m

ROLINE HD15 M/HD15 M avec noyaux de ferrite, 3,0m

ROLINE HQ VGA Cable + Ferrite, HD15, M/M, 3 m

|              |        |
|--------------|--------|
| CUSTOMER NO: | REMARK |
|              |        |




**NOTE:**

- 1) PRIMARY DIM:A,C,D
- 2) FULLY COPPER FOIL SHIELD 360°.
- 3) CABLE AND MODEL COLOR:BLACK
- 4) RoHS COMPLIANT

|    |  |
|----|--|
| 13 | NON UL PVC TUBE OD:2.3MM BLACK 6PCS RoHS                                 |
| 12 | UL HEAT SHRINK TUBE BLACK OD:1.5mm RoHS 6PCS                             |
| 11 | UL HEAT SHRINK TUBE BLACK OD:3.0mm RoHS 6PCS                             |
| 10 | SOLDER WIRE RoHS   |
| 9  | CABLE TIE BLACK 12cm RoHS  |
| 8  | COPPER W:0.024M RoHS 2PCS  |
| 7  | JUMP WIRE 24AWG 3CM RoHS   |
| 6  | FERRITE CORE #17.5X28.5X#9.5mm RoHS                                      |
| 5  | SCREW:#4-40UNC E:40.2MM BLACK(1101) RoHS                                 |
| 4  | INNER JACKET PE RoHS   |
| 3  | OUTER JACKET PVC 45Po BLACK(1101) RoHS                                   |
| 2  | HDB15M BLUE SOLDER TYPE TERMINAL PLATED GOLD FLASH W/O 9PIN RoHS         |
| 1  | UL2919 28#*3COAX+28#7C+AL+MY+B(1/65%)+D BALCK(1101) OD:8.0MM LENGTH RoHS |


**PINOUT:**



|  |               |                                     |          |
|--|---------------|-------------------------------------|----------|
| A  | FIRST EDITION | He X.Lin                            | 18/04/09 |
| REV. ECR   | DESCRIPTION   | C.N.                                | DATE     |
| <p>THESE DIMENSIONS AND SPECIFICATIONS ARE THE PROPERTY OF ROTRONIC CO. ANY REPRODUCTION OR USE WITHOUT THE WRITTEN PERMISSION OF ROTRONIC CO. IS STRICTLY PROHIBITED.</p> |               |                                     |          |
| <p>PLEASE CONTACT ROTRONIC COMPANY FOR MORE INFORMATION</p>  |               | <p>TITLE: <b>MONITOR CABLE</b></p>  |          |
| <p>DESIGNER: _____</p>   |               | <p>CHK: He X.Lin</p>                |          |
| <p>DATE: _____</p>   |               | <p>PROJ. NO: <b>W28SBK1MMXX</b></p> |          |
| <p>DATE: _____</p>   |               | <p>REV: <b>A</b></p>                |          |
| <p>DATE: _____</p>   |               | <p>DATE: _____</p>                  |          |

|              |        |
|--------------|--------|
| CUSTOMER NO: | REMARK |
|              |        |

| 客戶料號       | 長度(M) | 包裝方式                  | 紙箱尺寸  |       |       | 裝箱數量 |
|------------|-------|-----------------------|-------|-------|-------|------|
|            |       |                       | 高(cm) | 長(cm) | 寬(cm) |      |
| 11.04.5252 | 2.0   | 吊卡+PE袋(8"×10"×0.08mm) | 20    | 37    | 30    | 20   |
| 11.04.5253 | 3.0   | 吊卡+PE袋(8"×10"×0.08mm) | 17    | 46    | 30    | 20   |
| 11.04.5256 | 6.0   | 吊卡+PE袋(8"×10"×0.08mm) | 17    | 46    | 30    | 10   |
| 11.04.5260 | 10    | PE袋(9"×14"×0.08mm)    | 20    | 32.5  | 25    | 5    |
| 11.04.5270 | 20    | PE袋(12"×14"×0.08mm)   | 18    | 26    | 26    | 2    |
| 11.04.5280 | 30    | PE袋(14"×16"×0.08mm)   | 18.5  | 36.5  | 30    | 2    |



- NOTE:
- 1) 線材長度和PE BAG規格參表格.
  - 2) 貼紙由業務提供.
  - 3) 各長度的線材, 紙箱尺寸和裝箱數量參上表格.
  - 4) 產品符合RoHS標準.

|   |   |                                  |  |
|---|---|----------------------------------|--|
| A   | FIRST EDITION   | He X.Lin                         | 18/04/09   |
| REV. ECR  | DESCRIPTION   | C.N.                             | DATE   |
| <small>THIS DRAWING AND SPECIFICATIONS ARE THE PROPERTY OF ROTRONIC CO. ANY REPRODUCTION OR USE WITHOUT THE WRITTEN CONSENT OF ROTRONIC CO. IS STRICTLY PROHIBITED.</small> |   | <b>Rotronic Co., Ltd</b>         |  |
| <small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS (INCHES) TOLERANCES ARE:</small>  |   | <b>MONITOR CABLE</b>             |  |
| <small>DIMENSIONS</small><br>0.00 TO 25.00mm ±0.10mm<br>25.01 TO 50.00mm ±0.15mm<br>50.01 TO 100.00mm ±0.20mm<br>100.01mm ±0.25mm   | <small>TOLERANCES</small><br>±0.10mm<br>±0.15mm<br>±0.20mm<br>±0.25mm | <small>DRWD.</small><br>He X.Lin | <small>APPD.</small><br>He X.Lin   |
| <small>MATERIAL</small>   |   | <small>PROJ. NO.</small>         | <b>W28SBK1MMXX</b>   |
| <small>FINISH</small>   |   | <small>SCALE</small>             | <small>SHEET</small> 2/2 <small>UNIT</small> MM <small>PAGE</small> A4 <small>REV.</small> A |