

## Electronic depth callipers

IP40

**ORION**<sup>®</sup>

### Application:

For measuring, e. g. bore depths, shoulders on workpieces etc.

### Execution:

- ON/OFF
- Zero setting at any position
- mm/inch switch-over
- ABS function

### Delivery:

in a plastic case, with battery (1 x type SR44)



<b>Art. no.</b>	<b>31295 150</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	31295150
<b>Min./max. length measuring range</b>	0-500 mm
<b>Digit increment</b>	0.01 mm
<b>IP protection class</b>	IP 40
<b>Bridge length x bridge width</b>	150 x 9 mm
<b>Type of locating</b>	With locking screw
<b>Calibration Group</b>	B
<b>With automatic shut off</b>	Yes
<b>Number of rechargeable batteries/batteries</b>	1 PCS
<b>Display</b>	Digital
<b>Battery designation</b>	1,5 V SR44
<b>ISO</b>	13385-2
<b>Bridge length</b>	150 mm
<b>Gross Weight</b>	2.300 kg
<b>Product Group</b>	3BI

### EAN

4053625306473