

Electronic micrometer

With large measuring range

Mitutoyo

Application:

For measuring e.g. shank diameters, external dimensions of workpieces etc.

Execution:

- carbide-tipped measuring faces
- ABS function
- HOLD (measured value storage)

Advantage:

- 330° rotating display

Delivery:

Includes box, setting standard, adjustment wrench, two batteries



Art. no.	32017 402
Brand	MITUTOYO
Manufacturer Part Number	293-585
Display	Digital
Min./max. length measuring range	375-400 mm
Digit increment	0.001 mm
Measuring surface diameter	8 mm
IP protection class	IP 40
Data transmission type	DIGIMATIC
Spindle clamping	Yes
Digit height	7.5 mm
Functions	ABS function, Preset function, Hold-function (AE lock), Automatic switch-off
Min./max. measurement force	10-14 N
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
DIN	863
Measuring spindle increments	0.5 mm
Calibration Group	D
Gross Weight	6.600 kg
Product Group	3MA

EAN

49463686 10320