

## Letter marking stamp sets, font height 1 to 10 mm

Standard font, with impact depth limiter, nickel-plated

**ORION**<sup>®</sup>

### Application:

For labelling parts

### Execution:

- With depth limit
- Standard lettering
- Exactly in the centre
- DIN 1451 typeface
- Close-spaced lettering
- Hardness at end of writing: 58-60 HRC
- Maximum strength: 1200 N/mm<sup>2</sup>
- Nickel-plated

### Delivery:

In plastic box



<b>Art. no.</b>	<b>56932 015</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	56932015
<b>Character height</b>	1.5 mm
<b>Character type provided</b>	Letters
<b>Number of stamps</b>	27 PCS
<b>Length x width x height</b>	7 x 7 x 75 mm
<b>Surface</b>	Nickel plated
<b>With depth limiter</b>	Yes
<b>Gross Weight</b>	0.700 kg
<b>Product Group</b>	577

### EAN

4039247317196