

Handheld 2-Function





MSP-HH-AH-10100



Specifications & order information

Number of buttons	4	Dimensions	285x48x44mm
Number of functions	2, high/Low function and leg spread function	Replaces Arjo part number	HMX977/HMX977-1/ KPX00510.0
Connector	90° Hooked connector, 8-pin DIN	Packaging	Per piece, 50 pcs per box
Cable	Spiral cable 8x AWG26 1285 mm long	M.O.Q.	1 pcs
Materials	PPC, TPE, SS	Lead time	2-3 working days
Housing colour	Blue & gray	Approval	CE

Design enhancements

-  **Faster** operation due to larger control buttons
-  **More ergonomic** due to more comfortable hand control shape
-  **Suitable** for both left and right-handers
-  **More efficient** through touch confirmation and feedback sound

A smarter & safer alternative



100% compatible with 5+ leading patient hoists

- Sara 3000
- Sara Plus
- Tenor
- Maxi Move
- Ambulift and more

MDR Compliance

This product complies to MDR (EU) 2017/745 (EU MDR). This product is designed to restore the function off the device without affecting the performance and safety characteristics.

You can use this datasheet as a statement to competent EU authorities.

Explore more accessories or alternatives in our web shop



Wall Mounted Charger SLA 24V/DC

MSP-C-AH-00200




Charger SLA 24V/DC Table Model

MSP-C-AH-00600



Battery Pack 24V/DC 5Ah

MSP-A-AH-00120



All Day Sling Visual Clip

MSP-TB-AD-00310



Disposable Sling

MSP-TB-DP-00140HS



Corset Sling Visual Clip

MSP-TB-CT-00150