


# PX0101P02BK Datasheet

Product Name // PX0101P02BK

[View Product Page](#)



## // Product Description:

- Female Connectors
- Water and dustproof to IP68 when mated with compatible connector
- 2 Contact plug
- Crimp terminal
- Shrink Boot Adapter, Protective End Cap, Terminating Resistor, Enhanced Seal Protection available
- Y-Type and Welded flange available
- Mate with PX0100 Series, as appropriate
- Wedgelocks provided

## // General Information:

Product Configurator:	No
Product Display Title:	<h1>Rectangular Power Connector</h1>
Product Family:	Rectangular Power Connectors
Product Series:	Standard Rectangular Power Connector
Pdfbuilder Enabled:	Yes
Body Colour:	Black
Ip Rating:	IP68, IP69K
Max Operating Temperature:	+120°C
Min Operating Temperature:	-40°C
Number Of Contacts:	2 Contacts
Product Technical Image:	/p/x/px0101_diagram.jpg

## // Electrical Specifications:

Contact Type:	Plug Contact
Current Max:	13A
Voltage Max:	250V

## // Material Information:

Body Material:	Polycarbonate/Polybutylene Terephthalate (PC/PBT)
----------------	---

// Product PDF Links

[Rectangular Power Connector](#)

// Product 3D CAD Model Links

[PX0101P02BK3D CAD Model](#)