




CABLE/100M/PUR/4X0.34/OR

Accessories



**Product characteristics**

**Cable**

**Environment**

Ambient temperature [°C] -40...90, cRUUs: max. 80 °C

Ambient temperature (moving) [°C] -25...90, cRUUs: max. 80 °C

**Mechanical data**

**Drag chain suitability**

Bending radius for flexible applications: min. 10 x cable diameter  
max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s<sup>2</sup>  
Travel speed: 5 m/s<sup>2</sup>  
Bending cycles: > 2 million  
Torsional strain: ± 180 °/m

Weight [kg] 3.326

**Electrical connection**

**Connection**

PUR cable / 100 m;  
4 x 0.34 mm<sup>2</sup> (42 x Ø 0.1 mm); Ø 4.9 mm; not irradiated (can be recycled), halogen-free, resistant to welding sparks

**Sheath colour**

orange

**Wiring**

**Core colours**

- BK black
- BN brown
- WH white
- BU blue

**Remarks**

Pack quantity [piece] 1