

## MEN POWER SUPPLY 1/2-PHASE, SMOOTHED

IN: 230/400+/-15VAC OUT: :24V/20ADC


Current: 20 A

Output rating: 480 W


This power supply units meet the (EN 61000-3-2) standard for harmonic current.

### [Link to Product](#)

#### Illustration



stay connected



Product may differ from Image

### Approvals



### Input

Input voltage	230/400 ±15 V AC
Input current	3.7 A (230 V AC); 2.15 A (400 V AC)
Input fuse (external)	5 A (T) (230 V AC); 3.15 A (T) (400 V AC)
Frequency	50...60 Hz

### General data

Standards	(EN 55011 A)
Mounting method	Key-hole mounting
Dimensions H × W × D	127×174×213.5 mm
Fixing centers a × b × c	102×135×7 mm
Temperature range	-20...+60 °C, no condensation

### Output

Output voltage	24 V DC (SELV)
Output current (Ta 60/40 °C)	max. 20 A (230 V AC); 24 A (400 V AC)
Ripple	max. 5 %rms
Output filter	LED, VDR and smoothing capacitor

### Commercial data

country of origin	CZ
customs tariff number	85044090
minimum order quantity	1