



Datenblatt - Fiche technique - Data sheet

11.04.5656





ROLINE Monitor-Kabel mit Ferritkern+DDC, HD15 ST-ST, 6,0m

ROLINE Câble High Quality HD15 M/HD15 M avec noyaux de ferrite + DDC,
6,0m

ROLINE High Quality VGA Cable + Ferrite + DDC, HD15, M/M, 6 m

HD15PIN T/N:	D-073(B)
Ferrite T/N:	F-001

REV	DATE	REV.DIMENSION	DRAW	CHECK	APPROVE
1	07.02.27	NEW DRAWING	XHJ	Lshd	WJ



See Table:

Item no.	(L)
11.04.5652	2000 ± 50mm
11.04.5656	6000 ± 60mm

Electronic Test :

- 100% Test (Open, Short, Miss Wire)
- Contact Resistance : R ohm max
- Insulation Resistance : 10M ohm min
- Hi-Pot : 300V DC/10ms

NO.	P/N	DESCRIPTION	Q'TY	UNIT
⑦	R87-01001	Ferrite Core 17.5*9.5*28.5	2	pcs
⑥	R87-04005	Copper Foil 360° Solder W=3.2cm	12/100	m
⑤	R90-45006	Outside Molding 45P PVC PMS:Black 3U2X	72/1000	kg
④	R91-01001	Inside Molding PE	9.5/1000	kg
③	R86-20043	Screw 40.5mm #4-40UNC Color:Black 3U2X	4	pcs
②	R71-15009	HD15P Male Solder Type Insulation Blue	2	pcs
①	61-126XX	UL2919 28AWGx3Coax+24AWGx9C+AL/MY+DW+BD Jacket Color PMS:Black 3U2X OD:8.5±0.2	L	m

Rotronic		RoHS COMPLIANT			
		DESCRIPTION	VGA Cable HD15M/M 3Coax+9C Black		
HS CODE		CUSTOMER P/N			
UPC		MODEL NO.			
DRAW.	XHJ	ITEM NO.			
CHECK.	Lshd	DWG NO.	BA-72029	REV.	1
APP.	WJ	DATE.	07.02.27	SCALE.	NONE
		SIZE.	A4	UNIT.	mm
				SHEET	1/1