



Order symbol: TA111107
Product nbr: 5814039
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074011473
EI. number:
Finland: 3438268
Electric No. Denmark: 8212045224
Electric No. Sweden: 5814039

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:		Length	Width	Height	Accessories:		
mm:		110	110	65	DRM 80	DIN-15 Mounting rail	
inch:		4.3	4.3	2.6	FP 10674		
					DPS 14553	Grey sealing plug set	
Materials:						Rating:	
Material:	ABS					Ingress Protection (EN 60529): IP65	
Base colour:	RAL 7035 -light grey					Impact Resistance (EN 62262): IK07	
Cover screws material:	Polyamide					Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey					Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey					Flammability Rating: UL 94 HB	
Gasket material:	Polyurethane					Glow Wire Test (IEC 695-2-1) °C: 650	
Temperatures:						Certificates:	
Temperature °C (short term):	-40 ... 80 °C					SGS Fimko	
Temperature °C (continuous):	-40 ... 60 °C						
Temperature °F (short term):	-40 ... 175 °F						
Temperature °F (continuous):	-40 ... 140 °F						
Accessories:							
MP 1111	Mounting plate						

