

Main

| | |
|--------------|------------------------------------|
| Product line | QO |
| Product type | Load Center Grounding Bar Assembly |



Complementary

| | |
|---------------------------|---|
| Number of connectors | 15 |
| Wire size | AWG 14...AWG 4 copper AWG 12...AWG 4 aluminium |
| Provided equipment | 2 screw |
| Bar length | 5.63 in (143 mm) |
| Maximum length of segment | 3.15 in (80 mm) |
| Device mounting | Direct mounting back of enclosure |
| Tightening torque | 30 lb.in Mounting screw 30 lb.in 20 lb.in, AWG 14...AWG 10, copper 20 lb.in, AWG 12...AWG 10, aluminium 25 lb.in, AWG 8 35 lb.in, AWG 6...AWG 4 25 lb.in, AWG 14...AWG 12, copper 25 lb.in, AWG 12...AWG 10, aluminium |

Ordering and shipping details

| | |
|-----------------------|---------------------------|
| Category | 00102 - QO LC ACCESSORIES |
| Discount Schedule | DE3A |
| GTIN | 00785901026419 |
| Nbr. of units in pkg. | 10 |
| Package weight(Lbs) | 0.15 lb(US) (0.07 kg) |
| Returnability | Yes |
| Country of origin | US |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.40 in (1.016 cm) |
| Package 1 width | 1.70 in (4.318 cm) |
| Package 1 Length | 5.80 in (14.732 cm) |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 28.00 oz (793.786 g) |
| Package 2 Height | 3.70 in (9.398 cm) |
| Package 2 width | 6.30 in (16.002 cm) |
| Package 2 Length | 6.90 in (17.526 cm) |

| | |
|------------------------------|----------------------------|
| Unit Type of Package 3 | PAL |
| Number of Units in Package 3 | 2160 |
| Package 3 Weight | 411.00 lb(US) (186.426 kg) |
| Package 3 Height | 28.00 in (71.12 cm) |
| Package 3 width | 40.00 in (101.6 cm) |
| Package 3 Length | 48.00 in (121.92 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| California proposition 65 | WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|