


Category (ETIM):	Device mounts
Type:	Device mount IP20-SDGLDA LED
Order number:	18364504100
Configuration:	Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Operating device:	Electronic driver (1 pcs.)
Mains voltage:	230V / 50Hz
System performance (W):	47
Luminaire luminous flux (lm):	7500
lm/W:	158
Ambient temperatures:	10°C / 40°C
Certifications:	IP 20, protection class I, F, DIN10500/Food, Indoor, CE
Colour of the housing:	traffic white RAL 9016
Weight (net) (kg):	1.7
Dimensions LxWxH/DxH (mm):	1531 x 55 x 46
mounting method:	Mounting rail system mounting
EAN-number:	4020863336234
Commodity code:	94051098


## SDGLDA LED 7500lm 840 • vw • ED • 18364504100



**Lighting technology**  
 Linear.Lens.Profil-direct Batwing distribution  
 SDGLDA LED 7500 lm 840



ηLB	100 %
lm/W	158
Φ ↓/↑	98 % / 2 %
UGR q/l	23.2 / 26.9



Quick-fit mounting system Device mounts; Device mount made of galvanised, profiled sheet steel, surface coated with polyester resin enamel. Toolless fastening with two integrated lateral lever locks. LED unit in housing length for optically seamless light run. Housing colour traffic white RAL 9016; Direct, double asymmetric light distribution using Linear.Lens.Profil made of matt PMMA plastic. Optically seamless light run. Heat-resistant cables including fixed 3-pole rapid installation plug connector with tool-less phase pre-selection and locating finger.

Dimensions LxWxH/DxH (mm): 1531 x 55 x 46  
 Configuration: Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10  
 Luminaire luminous flux (lm): 7500  
 lm/W: 158  
 Operating device: Electronic driver (1 pcs.)  
 System performance (W): 47  
 Conditions: Suitable for use in ambient temperatures of 10°C to 40°C  
 Certifications: IP 20, protection class I, F, DIN10500/Food, Indoor, CE

Regiolux GmbH  
 Type: SDGLDA LED 7500 840 ET vw  
 Article number: 18364504100  
 Product deep link: <http://www.regiolux.de/de/article/18364504100>  
 5 year guarantee after registration on website.