

Conical countersink, 90°, HSSE, single-bladed cutter

For universal use up to 1300 N/mm²

ORION[®]

Application:

For producing 90° counterbores up to 1300 N/mm².

Execution:

- profile-ground single-edge countersink

Advantage:

- radial relief ensures optimum chip breaking
- deep and wide flute provides optimum chip removal



Art. no.	11497 905
Brand	ORION
Manufacturer Part Number	11497905
Countersink angle	90 Degree
Cutting material	HSSE
Surface	Uncoated
Number of cutting edges	1 PCS
Tool holding device	HA parallel shank
Spot-facer diameter	5 mm
Min./max. cutting edge diameter	1-5 mm
Shank diameter	5 mm
Length	50 mm
f steel 1000	0.07 mm/r
Gross Weight	0.010 kg
Product Group	1EH

EAN

4053625031078