

## Collet chucks type ER40 in accordance with DIN 6499 A

HP = high precision, concentricity < 5 µm

**ATORN**<sup>®</sup>

### Application

For use on precision collet chucks

### Advantage

- Higher concentricity extends tool life

<b>Art. no.</b>	<b>23388 133</b>
<b>Collet type</b>	ER 40
<b>Clamping diameter</b>	24.5 mm
<b>Min./max. clamping range</b>	3-26 mm
<b>Outer diameter</b>	41 mm
<b>Length</b>	46 mm
<b>Clamping bypass</b>	-0.5 mm



### EAN-Code

4050293631012