

SVS ECO VALVE PLUG FORM CI 9.4 MM 110V


3+PE field-wireable M11x1.75


Form CI (9.4 mm)
0...110 V AC/DC, without components
metric

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link to Product](#)

Illustration





Product may differ from Image

Form

30245

Technical Data

Operating voltage	0...110 V AC/DC
Operating current per contact	max. 6 A
Connection cross section	max. 0.5 mm ²
Sealing range (cable diameter)	5...6 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Contact figure	Cable outlet can be turned in 90° steps
Compression gland	M12 × 1.75 mm
Protection	IP65 inserted and tightened

General data

Temperature range	-25...+90 °C
-------------------	--------------

Commercial data

country of origin	HU
customs tariff number	85369010
minimum order quantity	1